FLZLCUCAG

Base Product



OM3 LC/UPC to Unconnectorized 36-Fiber InstaPATCH® 360 Ruggedized Fanout Cable, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot A Aqua
Color, connector A Black

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A LC/UPC

Interface, Connector B Unterminated

Jacket Color Aqua
Fibers per Subunit, quantity 12

Total Fibers, quantity 36


Dimensions

Cable Assembly Length Range (m)3 - 305Cable Assembly Length Range (ft)8 - 999

Ordering Tree



FLZLCUCAG



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM3, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C to} +60 \,^{\circ}\text{C (+14 °F to +140 °F)}$

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



<u>F</u>LZLCUCAG



Included Products

760093468 P-036-MP-5L-F12AQ


860637378

Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 36 fiber multi-unit with 12 fiber subunits,
 Multimode OM3, Gel-free, Feet jacket marking, Aqua jacket color

- LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode



760093468 | P-036-MP-5L-F12AQ



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 36 fiber multi-unit with 12 fiber subunits, Multimode OM3, Gel-free, Feet jacket marking, Aqua jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 12

Total Fiber Count 36

Dimensions

Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 9.1 mm | 0.358 in

Representative Image



760093468 | P-036-MP-5L-F12AQ



Mechanical Specifications

Minimum Bend Radius, loaded 136 mm | 5.354 in

Minimum Bend Radius, unloaded 91 mm | 3.583 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

FIEX Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM3, LazrSPEED® 300 | OM3, LazrSPEED® 300

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Operating Temperature $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$

Page 5 of 8



760093468 | P-036-MP-5L-F12AQ

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend 0 °C to +70 °C (+32 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

 Cable weight
 75 kg/km | 50.398 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



860637378

LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandLazrSPEED®

General Specifications

Body StyleDuplexColorBeige

Ferrule Geometry Pre-radiused

Interface LC/UPC

Dimensions

 Length
 50.3 mm | 1.98 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Multimode

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, ULL, maximum0.15 dBReturn Loss, minimum35 dB

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications



860637378

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

