ANXMXLCAD

Base Product



OM4 MPO12 (Pinned) to LC/UPC, Ruggedized Fanout Fiber Cable, 12-Fiber, Method A, Low Smoke Zero Halogen

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot ABlackColor, connector AAquaColor, boot BAquaColor, connector BBeigeConstruction TypeStranded

Furcation Color Aqua

Interface, Connector A MPO-12/UPC Male

Interface, Connector BLC/UPCJacket ColorAqua

Polarity Method A

Fibers per Subunit, quantity 12

Total Fibers, quantity 12

Dimensions


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 7 - 999

COMMSCOPE®

ANXMXLCAD

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

ANXMXLCAD

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant




Included Products

760067470 – Fiber Indoor Cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber, N-012-MP-5K-F12AQ/D Gel-free, Multimode OM4, Dca Flame Rating, Feet jacket marking, Aqua jacket color

860366228 – MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

860637378 – LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode

760067470 | N-012-MP-5K-F12AQ/D



Fiber Indoor Cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber, Gel-free, Multimode OM4, Dca Flame Rating, Feet jacket marking, Aqua jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Total Fiber Count 12

Dimensions


Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 5.4 mm | 0.213 in

Representative Image



760067470 | N-012-MP-5K-F12AQ/D



Mechanical Specifications

Minimum Bend Radius, loaded 81 mm | 3.189 in

Minimum Bend Radius, unloaded 54 mm | 2.126 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 5.88 N-m | 52.042 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Page 5 of 10

760067470 | N-012-MP-5K-F12AQ/D

Operating Temperature $-20 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Environmental Test Specifications

Heat Age $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-4 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

 Low High Bend
 -20 °C to +70 °C (-4 °F to +158 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 28 kg/km | 18.815 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 6 of 10



MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorAquaColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface FeaturePinnedTotal Fiber Count12

Dimensions

 Length
 60.1 mm | 2.366 in

 Compatible Cable Diameter
 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 ^{\circ}$

Optical Specifications

Fiber ModeMultimodeFiber TypeOM3 | OM4

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

COMMSCOPE®

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

Body StyleDuplexColorBeige

Ferrule Geometry Pre-radiused

Interface LC/UPC

Dimensions

 Length
 50.3 mm | 1.98 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Multimode

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, ULL, maximum0.15 dBReturn Loss, minimum35 dB

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications

COMMSC PE®

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

