## ALGMPLCAD

#### **Base Product**



Singlemode MPO12 (Unpinned) to LC/UPC, Ruggedized Fanout Cable, 12-Fiber, Method A, Plenum

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America	
Portfolio	CommScope®	
Product Type	Ruggedized fanout	
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters ( Minimum length may vary based on cable configuration	

#### General Specifications

Cable Assembly Length Range (ft)

Color, boot A	Black
Color, connector A	Green
Color, boot B	Blue
Color, connector B	Blue
Construction Type	Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Female
Interface, Connector B	LC/UPC
Jacket Color	Yellow
Polarity	Method A
Fibers per Subunit, quantity	12
Total Fibers, quantity	12
Dimensions	
Cable Assembly Length Range (m)	3 - 999

Page 1 of 10

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

7 - 999



# ALGMPLCAD

### Ordering Tree

	BASE	CODE			
Ja	cket Color		Breakout Length / Option		Length
J	Yellow	E	24 inch breakout, no gland		
		F	24 inch breakout, with gland		
		G	G 24 inch breakout, with pulling grip		
		S	36 inch breakout, no gland		
		U	36 inch breakout, with gland		UOM
		Т	36 inch breakout, with pulling grip	F	Feet
		н	48 inch breakout, no gland	М	Meter
		J	48 inch breakout, with gland		
		К	48 inch breakout, with pulling grip		
		L	72 inch breakout, no gland		
		М	72 inch breakout, with gland		
		Ν	72 inch breakout, with pulling grip		

#### Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °   4.40 lb @ 90 °
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	G.652.D   G.657.A2, TeraSPEED®

#### **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** 

Indoor | Plenum

#### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value

Page 2 of 10



# ALGMPLCAD

Compliant/Exempted

Compliant/Exempted

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS



#### Included Products

760038307 P-012-MP-8W-F12YL	-	Fiber indoor cable, TeraSPEED® Plenum for MPO Trunks, 12 fiber, Singlemode G.652.D and G. 657.A1, Feet jacket marking, Yellow jacket color
860637435	-	LC/UPC Connector, Singlemode, Blue, Short Boot
860638318	-	MP012, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm


Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 3 of 10



# 760038307 | P-012-MP-8W-F12YL



Fiber indoor cable, TeraSPEED® Plenum for MPO Trunks, 12 fiber, Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color

#### Product Classification


Regional Availability	Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	P-MP
General Specifications	
Cable Type	MPO trunk cable
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Feet
Total Fiber Count	12
Dimensions	
Buffer Tube/Subunit Diameter	3 mm   0.118 in
Diameter Over Jacket	4.9 mm   0.193 in

#### Representative Image

Page 4 of 10



# 760038307 | P-012-MP-8W-F12YL



#### Mechanical Specifications

Minimum Bend Radius, loaded	74 mm   2.913 in
Minimum Bend Radius, unloaded	49 mm   1.929 in
Tensile Load, long term, maximum	200 N   44.962 lbf
Tensile Load, short term, maximum	667 N   149.948 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	0.74 N-m   6.55 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	500 m   1,640.42 ft
Optical Specifications	

Fiber Type

G.652.D and G.657.A1, TeraSPEED  $\circledast ~\mid~$  OS2  $~\mid~$  OS2  $~\mid~$  OS2

#### **Environmental Specifications**

Installation temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

Page 5 of 10



# 760038307 | P-012-MP-8W-F12YL

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
Environmental Space	Plenum
Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 130   NFPA 262

#### Environmental Test Specifications

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

#### Packaging and Weights

#### Cable weight

23 kg/km | 15.455 lb/kft

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 6 of 10





Product Classification

#### LC/UPC Connector, Singlemode, Blue, Short Boot

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
General Specifications	
Color, boot	Blue
Color, housing	Blue
Interface	LC/UPC
Dimensions	
Length	41.6 mm   1.638 in
Material Specifications	
Ferrule Material	Zirconia
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Singlemode
Insertion Loss Change, mating	0.2 dB
Optical Components Standard	ANSI/TIA-568. 3-D   IEC 61753-1
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.25 dB
Return Loss, minimum	55 dB

### Regulatory Compliance/Certifications

Page 7 of 10



#### Agency

CHINA-ROHS

#### ROHS UK-ROHS

Classification

Below maximum concentration value Compliant Compliant



#### \* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 8 of 10





Product Classification

#### MP012, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	TeraSPEED®
General Specifications	
Color	Green
Color, boot	Black
Ferrule Geometry	Angled
Interface	MPO/APC Female
Interface Feature	Unpinned
Total Fiber Count	12
Dimensions	
Length	60.1 mm   2.366 in
Compatible Cable Diameter	3 mm   0.118 in
Material Specifications	
Ferrule Material	Polymer
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	G.652.D and G.657.A1, TeraSPEED®   OS2
Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568-C.3

Page 9 of 10



Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.35 dB
Return Loss, minimum	65 dB

#### Packaging and Weights

Packaging quantity

1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

#### \* Footnotes

Insertion Loss Change, mating	TIA-568: Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 10 of 10

