

# F4RS-HPDMDR-5M



HELIAX® 1/2" Superflexible Fire retardant SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Right Angle Male, 5 meter Black non-halogenated, fire retardant polyolefin jacket

## Product Classification

|                       |                                   |
|-----------------------|-----------------------------------|
| <b>Product Type</b>   | SureFlex® HP, HELIAX® performance |
| <b>Product Brand</b>  | HELIAX®   SureFlex®               |
| <b>Product Series</b> | RSJ4-50                           |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Right angle   |
| <b>Interface, Connector A</b>             | 7-16 DIN Male |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |                 |
|---------------------|-----------------|
| <b>Length</b>       | 5 m   16.404 ft |
| <b>Nominal Size</b> | 1/2 in          |

## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Static Test Method</b> | Two +43 dBm carriers |
| <b>3rd Order IMD, typical</b>           | -116 dBm             |
| <b>DTF, Connector A</b>                 | -34 dB               |
| <b>DTF, Connector B</b>                 | -34 dB               |

## VSWR/Return Loss

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 680–960 MHz    | 1.083         | 27.99                     |
| 1700–2200 MHz  | 1.083         | 27.99                     |
| 2200–2700 MHz  | 1.135         | 23.98                     |

# F4RS-HPDMDR-5M

## Jumper Assembly Sample Label



## Environmental Specifications

|  |   |
|--|---|
| EN50575 CPR Cable EuroClass Fire Performance | B2ca  |
| EN50575 CPR Cable EuroClass Smoke Rating     | s1a   |
| EN50575 CPR Cable EuroClass Droplets Rating  | d1  |
| EN50575 CPR Cable EuroClass Acidity Rating   | a1  |
| Immersion Test Method                        | Meets IEC 60529:2001, IP68 in mated condition |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |