

# CMAX-3030-43-V53

---

Cell-Max™ Low PIM Directional High Capacity Venue MIMO Antenna, 698–960 MHz and 1710–2700 MHz, 30-Deg, 4.30-10



## OBSOLETE

This product was discontinued on: January 31, 2018

### Replaced By:

CMAX-3030S-43-V53 Cell-Max™ Low PIM Directional High Capacity Venue MIMO Antenna, 698–960 MHz and 1710–2700 MHz, 30-Deg,

## Product Classification

<b>Product Type</b>	Indoor/outdoor antenna
<b>Product Brand</b>	Cell-Max™

## General Specifications


<b>Application</b>	Indoor/Outdoor
<b>Antenna Type</b>	Directional
<b>Polarization</b>	±45°
<b>Color</b>	White
<b>Number of Ports</b>	2
<b>Radome Material</b>	Fiberglass, UV resistant
<b>RF Connector Interface</b>	4.3-10 Female

## Dimensions

<b>Width</b>	740 mm   29.134 in
<b>Depth</b>	167 mm   6.575 in
<b>Length</b>	1060 mm   41.732 in

# CMAX-3030-43-V53

## Outline Drawing



## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>Lightning Protection</b>	dc Ground

## Electrical Specifications

Frequency Band, MHz	698-800	800-960	1695-1880	1850-1990	1920-2180	2200-2700	2300-2360
<b>Gain, dBi</b>	14.2	15.4	12.6	13.6	14.2	15.3	15
<b>Beamwidth, Horizontal, degrees</b>	34	29	38	35	32	28	29
<b>Beamwidth, Vertical, degrees</b>	34	29	38	35	32	28	29
<b>Horizontal Sidelobe, dB</b>	20	19	20	20	20	20	20
<b>Front-to-Back Ratio, Copolarization 180° ± 30°, dB</b>	30	32	32	34	34	36	36
<b>CPR at Boresight, dB</b>	20	24	18	18	18	18	18
<b>Isolation, Cross Polarization, dB</b>	23	23	23	23	23	23	23
<b>VSWR   Return loss, dB</b>	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
<b>PIM, 3rd Order, 2 x 20 W, dBc</b>	-153	-153	-153	-153	-153	-153	-153

# CMAX-3030-43-V53

<b>Input Power per Port, maximum, watts</b>	200	200	200	200	200	200	200
---	-----	-----	-----	-----	-----	-----	-----

## Mechanical Specifications

<b>Wind Loading @ Velocity, maximum</b>	2,128.0 N @ 216 km/h (478.4 lbf @ 216 km/h)
<b>Wind Speed, maximum</b>	216 km/h   134.216 mph

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP65
<b>Vibration Test Method</b>	ASTM D4169   IEC 60068-2-6

## Packaging and Weights

<b>Width, packed</b>	814 mm   32.047 in
<b>Depth, packed</b>	247 mm   9.724 in
<b>Length, packed</b>	1424 mm   56.063 in
<b>Included</b>	Mounting bracket
<b>Net Weight, with mounting kit</b>	26 kg   57.32 lb
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	38 kg   83.776 lb
<b>Weight, net</b>	20 kg   44.092 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

