

760239237 | 12" Pole Base 4G/5G, Round



Round 12 inch diameter, Integrated Pole Base Concealment Pole for 4G /5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Pole top concealment module for LAA/CBRS radio mounting
- Base of 12in diameter accepts up to (4) low power radios
- Concealment integrates AC load center/OVP and disconnect

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

ANDREW Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

Product Classification

| | |
|----------------------|-------------------------------------|
| Product Type | Integrated pole |
| Product Brand | Metro Cell |
| Ordering Note | ANDREW® standard product with terms |
| Warranty | One year |

General Specifications

| | |
|---|--|
| Antenna Compatibility, ANDREW | ANDREW Canister Antennas |
| Antenna Compatibility, Other Vendors | ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER |
| Antennas Included | None |
| Color | Light Gray (RAL 7035) |
| Color Options | Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver White (RAL 9010) |
| Compatible Foundation Type | Poured Concrete Pre-Cast Concrete |
| Compatible Smart Devices | Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI |
| Cooling | Passive Cooling |
| Radio Compatibility, ANDREW | CAP H |

760239237 | 12" Pole Base 4G/5G, Round

| | |
|--------------------------------------|--|
| Radio Compatibility, Ericsson | (3) 2205/2208 (Pole Top) (4) 2203 (radio concealment module) 220x 440x 4435 6701 6705 |
| Radio Compatibility, Nokia | (2) Airscale Micro Radios - LAA & CBRS (Pole Top) (2) Airscale micro radios - (radio concealment module) AHIA AHIB AZRB Airscale micro |
| Radios Included | None |

Dimensions

| | |
|----------------------------|--|
| Height Note | 5 ft tall Equipment Base 5.5 ft tall Radio Concealment Module |
| Pole Height Options | 10.668 m 35 ft 12.192 m 40 ft 6.096 m 20 ft 7.62 m 25 ft 9.144 m 30 ft |
| Depth | 325.12 mm 12.8 in |
| Depth Note | Round |
| Pole Diameter | 203.2 mm 8 in |

Electrical Specifications

| | |
|--------------------------|--|
| Power/Fiber Input | AC load center with OVP and disconnect |
|--------------------------|--|

Material Specifications

| | |
|----------------------------------|---------------|
| Finish Aluminum | Chromate |
| Finish Concealment Covers | Powder coated |
| Material Type | Steel |

Environmental Specifications

| | |
|---------------------------|--------|
| Thermal Compliance | GR-487 |
|---------------------------|--------|