

760242726 | 12" Straight Integrated Pole 4G only



Straight 12inch diameter, Integrated 4G only, Concealment Pole, to house and conceal four low-power radios and any other wireless infrastructure equipment inside pole modules. Accommodates ANDREW Cap-H in separate radio module.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment inside pole modules
- Includes everything needed for a low-power 4G outdoor small cell site
- Up to 4 low power radios, integrated AC load center/OVP and Disconnect , PoleTop concealment module for LAA/DBRS radio mounting

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

ANDREW Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

Product Classification

Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver White (RAL 9010)
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Cooling	Passive Cooling
Radio Compatibility, ANDREW	CAP H
Radio Compatibility, Ericsson	(3) 2205/2208 (Pole Top) (4) 2203 (radio concealment module) 220x 440x 4435

760242726 | 12" Straight Integrated Pole 4G only

Radio Compatibility, Nokia (2) Airscale Micro Radios - LAA & CBRS (Pole Top) | (2) Airscale micro radios – (radio concealment module) | AHIA | AHIB | AZRB | Airscale micro

Radios Included None

Dimensions

Height Note 5.5 ft tall Radio Concealment Module | 8 ft tall Power Module Base

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Depth 325.12 mm | 12.8 in

Depth Note Round

Pole Diameter 325.12 mm | 12.8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487