



## PICABOND® Connector, 250 loose piece, green

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

### OBSOLETE

This product was discontinued on: March 15, 2020

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Splice
<b>Product Brand</b>	PICABOND®
<b>Product Series</b>	PICABOND

## General Specifications

<b>Connector Color Code</b>	Green
<b>Connector Sealant</b>	Unfilled
<b>Connector Splicing Type</b>	Bridge   Butt   Full bridge   Half-tap   Straight (In-line)

## Dimensions

<b>Compatible Conductor Gauge, solid</b>	26–22 AWG
--	-----------

## Electrical Specifications

<b>Safety Voltage Rating</b>	400 Vdc
------------------------------	---------

## Material Specifications

<b>Contact Base Material</b>	Phosphor Bronze
<b>Contact Plating Material</b>	Tin
<b>Insulation Material</b>	Air Core PIC   Paper or Pulp

# 1-60945-3

---

## Environmental Specifications

**Operating Temperature** -40 °C to +60 °C (-40 °F to +140 °F)

**Environmental Space** Outdoor

## Packaging and Weights

**Packaging quantity** 250

**Packaging Type** Loose piece

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

