884039608/10 | CS44Z3 GRY C6A 4/23 F/UTP RL

CS44Z3 Category 6A, F/UTP Cable, low smoke zero halogen, gray jacket, 4 pair count, 1000ft (305 m) length reel

Product Classification

Regional Availability

Asia | Latin America

Portfolio NETCONNECT®

Product Type Twisted pair cable

Product Series 640 Series

General Specifications

ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type F/UTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Jacket ColorGray

Pairs, quantity 4

Transmission Standards ANSI/TIA-568.2-D | CENELEC EN 50288-6-1 | ISO/IEC 11801 Class EA

Dimensions

 Cable Length
 304.8 m | 1000 ft

 Diameter Over Jacket, nominal
 7.595 mm | 0.299 in

Conductor Gauge, singles 23 AWG

Electrical Specifications

Nominal Velocity of Propagation (NVP) 69% Operating Voltage, maximum 80%

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

Page 1 of 2



884039608/10 | CS44Z3 GRY C6A 4/23 F/UTP RL 305M

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Segregation Class

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Shield (Tape) Material Aluminum/Polyester

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Operating Temperature $-20 \,^{\circ}\text{C to} + 75 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} + 167 \,^{\circ}\text{F}\right)$

Acid Gas Test Method IEC 60754-2
Flame Test Method IEC 60332-3-22
Smoke Test Method IEC 61034-2

Packaging and Weights

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



