760249722 | C-006-CA-5Y-M06BK/28G/093



Fiber indoor/outdoor drop cable, LSZH, Gel-filled Central Tube, CST, 6 fiber, Multimode OM3, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

 Portfolio
 CommScope®

 Product Type
 Fiber drop cable

Product Series O-DA

General Specifications

Cable TypeCentral loose tube

Construction Type Armored

Fiber Type, quantity 6
Fibers per Subunit, quantity 6

Jacket ColorBlackJacket MarkingMetersSubunit TypeGel-filled

Total Fiber Count 6

Dimensions

Buffer Tube/Subunit Diameter2.8 mm | 0.11 inDiameter Over Jacket8.7 mm | 0.343 in

Mechanical Specifications

Minimum Bend Radius, loaded17.4 cm | 6.85 inMinimum Bend Radius, unloaded8.7 cm | 3.425 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum1500 N | 337.214 lbfCompression15 N/mm | 85.652 lb/in

Page 1 of 3



760249722 | C-006-CA-5Y-M06BK/28G/093

Compression Test Method IEC 60794-1-2 E3

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-2-E1

Optical Specifications

Fiber Type OM3

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Buried | Ducted | Indoor/Outdoor

Flame Test Method | IEC 60332-1 | IEC 60332-3-24

Water Penentration 24 h

Water Penentration Test Method IEC 60794-1 F5B

Environmental Test Specifications

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 95 kg/km | 63.837 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



* Footnotes



760249722 | C-006-CA-5Y-M06BK/28G/093

Operating Temperature Specification applicable to non-terminated bulk fiber cable

