ETL Verified Category 5e U/UTP Cable, non-plenum, gray jacket, 4 pair count, 1000 ft (305 m) length, CommPak

Product Classification


| Regional Availability | Asia |
|-------------------------------|--|
| Portfolio | CommScope® |
| Product Type | Twisted pair cable |
| Ordering Note | Available in Asia Pacific |
| General Specifications | |
| Product Number | CS24 |
| ANSI/TIA Category | 5e |
| Cable Component Type | Horizontal |
| Cable Type | U/UTP (unshielded) |
| Conductor Type, singles | Solid |
| Conductors, quantity | 8 |
| Jacket Color | Gray |
| Note | All electrical transmission tests include swept frequency measurements |
| Pairs, quantity | 4 |
| Transmission Standards | ANSI/TIA-568.2-D CENELEC EN 50288-3-1 ISO/IEC 11801 Class D |
| Dimensions | |
| Cable Length | 304.8 m 1000 ft |
| Diameter Over Jacket, nominal | 4.902 mm 0.193 in |
| Jacket Thickness | 0.508 mm 0.02 in |
| Conductor Gauge, singles | 24 AWG |

Cross Section Drawing

Page 1 of 4

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: June 28, 2022





Electrical Specifications

| Characteristic Impedance | 100 ohm |
|----------------------------------|---|
| dc Resistance Unbalance, maximum | 5 % |
| dc Resistance, maximum | 9.38 ohms/100 m 2.859 ohms/100 ft |
| Dielectric Strength, minimum | 1500 Vac 2500 Vdc |
| Mutual Capacitance at Frequency | 5.6 nF/100 m @ 1 kHz |
| Operating Frequency, maximum | 100 MHz |
| Operating Voltage, maximum | 80 V |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |
| Safety Voltage Rating | 300 V |

Page 2 of 4

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: June 28, 2022



Electrical Cable Performance

| CS | CommScope | | | | |
|--------|---|--------|---|--|--|
| STD | Refers to the standard value listed under Transmission Standards in the Electrical Specifications above | | | | |
| ТҮР | Typical Electrical Performance | | | | |
| IL | Insertion Loss (dB/100m) | NEXT | Near End Crosstalk (dB/100m) | | |
| ACR | Attenuation to Crosstalk Ratio (dB/100m) | PSNEXT | Power Sum Near End Crosstalk (db/100m) | | |
| PSACR | Power Sum Attenuation to Crosstalk Ratio (dB/100m) | ACRF | Attenuation to Crosstalk Ratio - Far End (dB/100m) | | |
| PSACRF | Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) | RL | Return Loss (dB) | | |
| TCL | Transverse Conversion Loss (dB/100m) | ELTCTL | Equal Level Transverse Conversion Transfer Loss (dB/100m) | | |

| Freq. | IL | NEXT | ACR | PSNEXT | PSACR | ACRF | PSACRF | RL |
|-------|------|------|------|--------|-------|------|--------|------|
| MHz | STD | STD | STD | STD | STD | STD | STD | STD |
| 1 | 2 | 65.3 | 63.3 | 62.3 | 60.3 | 63.8 | 60.8 | 20 |
| 4 | 4.1 | 56.3 | 52.2 | 53.3 | 49.2 | 51.8 | 48.8 | 23 |
| 8 | 5.8 | 51.8 | 46 | 48.8 | 43 | 45.7 | 42.7 | 24.5 |
| 10 | 6.5 | 50.3 | 43.8 | 47.3 | 40.8 | 43.8 | 40.8 | 25 |
| 16 | 8.2 | 47.2 | 39 | 44.2 | 36 | 39.7 | 36.7 | 25 |
| 20 | 9.3 | 45.8 | 36.5 | 42.8 | 33.5 | 37.8 | 34.8 | 25 |
| 25 | 10.4 | 44.3 | 33.9 | 41.3 | 30.9 | 35.8 | 32.8 | 24.3 |
| 31.25 | 11.7 | 42.9 | 31.2 | 39.9 | 28.2 | 33.9 | 30.9 | 23.6 |
| 62.5 | 17 | 38.4 | 21.4 | 35.4 | 18.4 | 27.9 | 24.9 | 21.5 |
| 100 | 22 | 35.3 | 13.3 | 32.3 | 10.3 | 23.8 | 20.8 | 20.1 |

Material Specifications

| Conductor Material | Bare copper |
|---------------------------|-------------|
| Insulation Material | Polyolefin |
| Jacket Material | PVC |
| Mechanical Specifications | |

| Pulling Tension, maximum | 11.34 kg 25 lb |
|--------------------------|------------------|
|--------------------------|------------------|

Environmental Specifications

| o +60 °C (+32 °F to +140 °F) |
|------------------------------|
| to +60 °C (-4 °F to +140 °F) |
| lenum |
| UL 1685 |
| |

Packaging and Weights

Packaging Type

Page 3 of 4

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: June 28, 2022

CommPak® box



Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS



Below maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant

Page 4 of 4

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: June 28, 2022

