

13 dB Coaxial Attenuator DC-6000 4.3-10 M-F

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Attenuator

General Specifications

Device TypeAttenuatorApplicationIndoorColorSilverInner Contact PlatingSilver

Interface 4.3-10 Male
Interface 2 4.3-10 Female

Outer Contact Plating Trimetal

Electrical Specifications

Return Loss, minimum20.8 dBAttenuation13 dBAttenuation Tolerance±0.5 dBAverage Power, maximum2 WImpedance50 ohm

Operating Frequency Band 0 – 6000 MHz

Peak Power, maximum 0.5 kW VSWR 1.2

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Regulatory Compliance/Certifications



AT-13-43-MF

Agency

Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

