

CQX782123T-DS-43 | E14F15P26



Twin Quadplexer, 700/850/PCS-AWS/WCS,DC Sense, 4.3-10

- BTS-to-feeder and feeder-to-antenna application
- Automatic dc switching with dc sense
- Convertible mounting brackets
- New 4.3-10 connectors for improved PIM performance and size reduction
- DC Load Sense in Feeder-to-Antenna applications

Product Classification

Product Type Quadplexer

General Specifications

Color Gray

Common Port Label Common

Modularity 2-Twin

Mounting Pole | Wall

RF Connector Interface 4.3-10 Female

RF Connector Interface Body Style Long neck

Dimensions

Height 202 mm | 7.953 in


Width 248 mm | 9.764 in

Depth 114 mm | 4.488 in

Ground Screw Diameter 6 mm | 0.236 in

Outline Drawing

CQX782123T-DS-43 | E14F15P26



Electrical Specifications

| | |
|--------------------------------|--|
| Impedance | 50 ohm |
| License Band, Band Pass | AWS 1700 CEL 850 LMR 750 PCS 1900 USA 700 USA 750 WCS 2300 |

Electrical Specifications, dc Power/Alarm

| | |
|---|-----------------------------|
| dc/AISG Pass-through Method | Auto sensing |
| dc/AISG Pass-through Path | See logic table |
| Lightning Surge Current | 5 kA |
| Lightning Surge Current Waveform | 8/20 waveform |
| Operating Current at Voltage | 15 mA @ 12 V 15 mA @ 24 V |
| Voltage | 7-30 Vdc |

CQX782123T-DS-43 | E14F15P26

Electrical Specifications, AISG

| | |
|--------------------------------|--------------------|
| AISG Carrier | 2176 KHz ± 100 ppm |
| Insertion Loss, maximum | 1 dB |
| Return Loss, minimum | 15 dB |


Electrical Specifications

| | | | | |
|-------------------------|--|--------------------|---------------------|---------------------|
| Sub-module | 1 | 1 | 1 | 1 |
| Branch | 1 | 2 | 3 | 4 |
| Port Designation | 698–798 | 824–894 | AWS-PCS | WCS |
| License Band | LMR 750, Band Pass USA 700, Band Pass USA 750, Band Pass | CEL 850, Band Pass | PCS 1900, Band Pass | WCS 2300, Band Pass |

Electrical Specifications, Band Pass

| | 698–798 | 824–894 | 1695–2200 | 2305–2360 |
|---------------------------------------|-------------------|-------------------|--|-------------------|
| Frequency Range, MHz | | | | |
| Insertion Loss, typical, dB | 0.3 | 0.3 | 0.3 | 0.3 |
| Total Group Delay, maximum, ns | 40 | 40 | 20 | 25 |
| Return Loss, minimum, dB | 20 | 20 | 20 | 20 |
| Isolation, minimum, dB | 50 | 50 | 50 | 50 |
| Input Power, RMS, maximum, W | 200 | 200 | 200 | 200 |
| Input Power, PEP, maximum, W | 2000 | 2000 | 2000 | 2000 |
| 3rd Order PIM, minimum, dBc | -155 | -155 | -155 | |
| 3rd Order PIM Test Method | 2 x 20 W CW tones | 2 x 20 W CW tones | 1 x 20 W AWS CW tone 1 x 20 W PCS CW tone | |
| Higher Order PIM, minimum, dBc | | | | -155 |
| Higher Order PIM Test Method | | | | 2 x 20 W CW tones |

Block Diagram



Logic Table

| Combining Mode Operation (Bottom) | | | | | | |
|-----------------------------------|--------------------|--------------------|--------------------|----|---|------------------------|
| RF Ports Input Voltage | | | | | COMMON | DC/AISG Path Selection |
| 698-798 MHz | 824-894 MHz | 1695-2200 MHz | 2305 to 2360 MHz | | | |
| Any* | Any* | $7 \leq V \leq 30$ | Any* | <7 | 698-798 MHz "OFF" 824 to 894 MHz "OFF" 1695-2200 MHz to COMMON "ON" 2305 to 2360 MHz "OFF" | |
| $7 \leq V \leq 30$ | Any* | <7 | Any* | <7 | 698-798 MHz to COMMON "ON" 824-894 MHz "OFF" 1695-2200 MHz "OFF" 2305 to 2360 MHz "OFF" | |
| <7 | Any* | <7 | $7 \leq V \leq 30$ | <7 | 698-798 MHz "OFF" 824-894 MHz "OFF" 1695-2200 MHz "OFF" 2305 to 2360 MHz to COMMON "ON" | |
| <7 | $7 \leq V \leq 30$ | <7 | <7 | <7 | 698-798 MHz "OFF" 824-894 MHz to COMMON "ON" 1695-2200 MHz "OFF" 2305 to 2360 MHz "OFF" | |
| <7 | <7 | <7 | <7 | <7 | ALL PORTS OFF | |

* Any DC voltage applied in the ON (7-30V) or OFF (<7V) ranges

| Splitting Mode Operation (Tower Top) | | | | | | |
|--------------------------------------|-------------|--------------|------------------|--------------------|--------------------|---|
| RF Ports Impedance DC (Load Sense) | | | | | COMMON | DC/AISG Path Selection |
| 698-798 MHz | 824-894 MHz | 1695-2200MHz | 2305 to 2360 MHz | | | |
| Short | Short | Short | Short | $7 \leq V \leq 30$ | ALL PORTS OFF | |
| Open/ Load | Open/ Load | Open/ Load | Open/ Load | $7 \leq V \leq 30$ | ALL PORTS ON | |
| One or more port(s) are Open/ Load | | | | | $7 \leq V \leq 30$ | DC/AISG will be passed to ALL Open/Load port(s) |

Note: In this mode DC/AISG will be passed to all detected ports and blocked at shorted ones

Environmental Specifications

Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)

Corrosion Test Method IEC 60068-2-11, 30 days

Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

Included Mounting hardware

Volume 5.7 L

Weight, without mounting hardware 6.8 kg | 14.991 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.andrew.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

