## C-30-TCPUSEW-N-AI6



Product Classification

#### 30 dB, Air Directional Coupler, 340-3800 MHz

PIUUULI LIASSIIILALIUII	
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Product Type	Directional coupler
General Specifications	
Device Type	Coupler
Application	Indoor/Outdoor
Color	White
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal
Dimensions	
Height	23 mm   0.906 in
Width	74.6 mm   2.937 in
Length	209.5 mm   8.248 in
Electrical Specifications	
3rd Order IMD	-163 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss at Frequency Band	0.25 dB @ 340-3800 MHz
Average Power, maximum	200 W
Coupling	30 dB
Coupling Tolerance	±1.6dB
Impedance	50 ohm
Isolation at Frequency Band	40 dB @ 2700-3800 MHz   46 dB @ 340-2700 MHz
Operating Frequency Band	340 – 3800 MHz
Peak Power, maximum	1 kW

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023



# C-30-TCPUSEW-N-AI6

Reflected Power, maximum	40 W
VSWR at Frequency Band	1.2:1 @ 340-2700 MHz   1.3:1 @ 2700-3800 MHz
Mechanical Specifications	
Coupling Nut Proof Torque	4.5 N-m   39.828 in lb

#### **Environmental Specifications**

Operating Temperature	-25 °C to +85 °C (-13 °F to +185 °F)
Relative Humidity	Up to 100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67

## Packaging and Weights

Height, packed	77 mm   3.031 in
Width, packed	42 mm   1.654 in
Length, packed	258 mm   10.157 in
Weight, gross	0.604 kg   1.332 lb
Weight, net	0.53 kg   1.168 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023

