

CA177B2

GigaSPEED X10D® M-series HGS620 to M-series HGS620 on 2291 Plenum Cable F/UTP Pre-terminated Cord

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair patch cord
Product Brand	GigaSPEED X10D®
Product Series	CA
Ordering Note	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

General Specifications

ANSI/TIA Category	6A
Cable Type	F/UTP (shielded)
Conductor Type	Solid
Information Outlet Color	Black Blue Ivory Orange Red
Interface, Connector A	Information outlet
Interface Feature, connector A	Standard
Interface, Connector B	Information outlet
Interface Feature, connector B	Standard
Jacket Color	Blue Slate
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4
Wiring	T568B

Dimensions

Cable Assembly Length Range (m)	1 – 100
Cable Assembly Length Range (ft)	1 – 328
Diameter Over Jacket	7.01 mm 0.276 in
Compatible Conductor Gauge, solid	23 AWG

CA177B2

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Electrical Specifications

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V

Ordering Tree

CA - ⁹ ¹⁰ ¹¹ ¹²

Outlet Color

0	Not applicable
1	Black
2	Blue
3	Gray
4	Green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac

Jacket Color

1	Black
2	Light blue
3	Dark gray
4	Spring green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac
C	Gray
K	Pink
L	Violet
M	Green
Z	Blue

UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

Length

12	XXX
----	-----

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

CA177B2

Contact Plating Material	Precious metals
Material Type	Copper alloy Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 29.9 lbf

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum
Flammability Rating	UL 94 V-0
Safety Standard	ETL cETL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

