



## CommScope® Category 6A U/UTP Cord, Plenum, RJ45 to Ceiling connector, 3 ft, white

- Perfect solution for connected devices in the ceiling: IP cameras, Wi-Fi access points and in-building wireless systems, LED lighting and sound masking systems
- For installation in difficult-to-access areas
- Provides a high-quality cable interconnection, available as a standalone unit or pre-terminated to an RJ45 plug
- Can be ordered individually or with a UTP pigtail, in plenum or low smoke zero halogen (LSZH) options
- Category 5e, 6 and 6A UTP can be terminated in the ceiling connector

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Twisted pair patch cord

## General Specifications

<b>ANSI/TIA Category</b>	6A
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Solid
<b>Interface, Connector A</b>	Ceiling connector
<b>Interface Feature, connector A</b>	Standard
<b>Interface, Connector B</b>	RJ45 plug
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4
<b>Wiring</b>	T568B

## Dimensions

<b>Cord Length</b>	0.91 m   2.986 ft
<b>Compatible Conductor Gauge, stranded</b>	24 AWG

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

### Material Specifications

<b>Contact Plating Material</b>	Precious metals
<b>Material Type</b>	Copper alloy   High-impact, flame retardant, thermoplastic

### Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	750 times
<b>Plug Retention Force, minimum</b>	133 N   29.9 lbf

### Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Environmental Space</b>	Plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ETL   cETL

### Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

# C01SJO2-88F003 | CCA-CAT6A-WH-3FT

---

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

760234921 CCA-WH	- Unshielded Ceiling Connector Assembly (CCA) without cordage, White
---------------------	-------------------------------------------------------------------------



## Unshielded Ceiling Connector Assembly (CCA) without cordage, White

- Perfect solution for connected devices in the ceiling: IP cameras, Wi-Fi access points and in-building wireless systems, LED lighting and sound masking systems
- For installation in difficult-to-access areas
- Provides a high-quality cable interconnection, available as a standalone unit or pre-terminated to an RJ45 plug
- Can be ordered individually or with a UTP pigtail, in plenum or low smoke zero halogen (LSZH) options
- Category 5e, 6 and 6A UTP can be terminated in the ceiling connector

### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio**

CommScope®

**Product Type**

Connector kit

### General Specifications

**ANSI/TIA Category**

6 | 6A

**Cable Type**

U/UTP (unshielded)

**Color**

Electrical white

**Conductor Type**

Solid | Stranded

### Dimensions

**Height**

27.178 mm | 1.07 in

**Width**

35.56 mm | 1.4 in

**Depth**

51.816 mm | 2.04 in

**Compatible Conductor Gauge, solid**

26–22 AWG

**Compatible Conductor Gauge, stranded**

26–22 AWG

### Electrical Specifications

**Contact Resistance Variation, maximum**

20 mOhm

**Contact Resistance, maximum**

100 mOhm

**Current Rating at Temperature**

1.5 A @ 20 °C | 1.5 A @ 68 °F

**Dielectric Withstand Voltage, RMS, contact-to-contact**

1,000 Vac @ 60 Hz

**Insulation Resistance, minimum**

500 MOhm

## Material Specifications

<b>Contact Plating Material</b>	Precious metals
<b>IDC Termination Material</b>	Phosphor Bronze
<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Phosphor Bronze

## Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	750 times
<b>Plug Retention Force, minimum</b>	44.645 kg/m   30 lb/ft

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)   Plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ETL   cETL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

