## 760249719 | C-006-CA-8Z-M06BK/28G/093



Fiber indoor/outdoor drop cable, LSZH, Gel -filledCentral Tube, CST, 6 fiber, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand

 Portfolio
 CommScope®

 Product Type
 Fiber drop cable

Product Series O-DA

## General Specifications

Cable Type Central loose tube

Construction Type Armored

Fiber Type, quantity 6
Fibers per Subunit, quantity 6

Jacket ColorBlackJacket MarkingMetersSubunit TypeGel-filled

**Total Fiber Count** 6

#### Dimensions

Buffer Tube/Subunit Diameter2.8 mm | 0.11 inDiameter Over Jacket8.7 mm | 0.343 in

### Mechanical Specifications

Minimum Bend Radius, loaded17.4 cm | 6.85 inMinimum Bend Radius, unloaded8.7 cm | 3.425 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum1500 N | 337.214 lbfCompression15 N/mm | 85.652 lb/in

Page 1 of 3



# 760249719 | C-006-CA-8Z-M06BK/28G/093

**Compression Test Method** IEC 60794-1-2 E3

**Strain** See long and short term tensile loads

Strain Test Method IEC 60794-1-2-E1

**Optical Specifications** 

**Fiber Type** G.652.D and G.657.A1 | OS2

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.22 dB/km @ 1,550 nm | 0.36 dB/km @ 1,310 nm

**Environmental Specifications** 

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Environmental Space Buried | Ducted | Indoor/Outdoor

Flame Test Method | IEC 60332-1 | IEC 60332-3-24

Water Penentration 24 h

Water Penentration Test Method IEC 60794-1 F5B

**Environmental Test Specifications** 

**Temperature Cycle**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** IEC 60794-1-2 F1

Packaging and Weights

**Cable weight** 95 kg/km | 63.837 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



\* Footnotes



# 760249719 | C-006-CA-8Z-M06BK/28G/093

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

