

CHP Max Headend Optics Platform

CHP-R2RRX*-30-S, CHP-2RRX*-30-S

Redundant/Non-Redundant Dual Return Path Receivers

FEATURES

- 300 MHz return path bandwidth meeting DOCSIS® 3.1 requirements
- Optimize headend and hub efficiencies with industry leading density and low power consumption
- Front or Rear Fiber options maximize cabling efficiency
- Improve system uptime with automatic failover option
- Configure, monitor, and manage with CORView™ Element Management System
- Automatic Gain Control feature to allow for better level control with redundancy

The CHP Dual Return Path Receiver is an integral part of a flexible return path system. Designed to operate as either a stand-alone or redundant module, the CHP Dual Receiver allows operators to increase their network capacity while reducing operational power. With support for up to 300 MHz of return bandwidth, the CHP Dual Receiver is an ideal choice for supporting future DOCSIS 3.1 band splits without having to upgrade receivers.

The CHP Dual Return Path Receiver accepts two optical inputs into a single-wide module, which supports up to 20 receivers in a single 2RU CHP chassis and up to 400 receivers in a standard 40RU rack. As operators add bandwidth to their networks, the CHP Dual Receiver can help them to achieve a migration path to DOCSIS 3.1 bandwidth. There is a front or rear fiber SC/APC connector option for the CHP Dual Return Path Receiver.



The CHP Dual Receiver is available in both redundant and non-redundant configurations. The redundant model protects both the optical path and vital hardware for VoIP, business data services, and other critical applications. For additional protection, the redundant model's integral optical and RF switches alternate between diverse paths when the receiver detects an optical path module hardware fault. In these instances, switch time is less than 50 milliseconds. Operators can pair redundant and non-redundant modules in either the same CHP chassis or in a spare chassis up to 6 meters away.

The CHP Dual Receiver offers high RF output with excellent power efficiency, typically consuming less than 3 Watts per RF channel. The modules are hot-swappable to ensure minimal loss of uptime. The receiver's Craft Graphical User Interface (GUI) provides local monitoring, configuration control, and firmware downloads, while the System Management Module (SMM) provides local and remote IP access to the Craft GUI, firmware downloads, and the SNMP HMS interface.

Automatic Gain Control allows for user to set the RF output level and have a window of optical input range to maintain the set output.

SPECIFICATIONS

Characteristics	CHP-R2RRX*-30-S	CHP-2RRX*-30-S
Physical		
Dimensions	1.25 in W x 3.44 in H x 18.5 in W (3.18 cm x 8.74 cm x 46.99 cm)	1.25 in W x 3.44 in H x 18.5 in W (3.18 cm x 8.74 cm x 46.99 cm)
Weight	3.0 lb (1.35 kg)	3.0 lb (1.35 kg)
Environmental		
Operating Temperature Range	0° to 50°C (32° to 122°F)	0° to 50°C (32° to 122°F)
Storage Temperature Range	-20° to 60°C (-4° to 140°F)	-20° to 60°C (-4° to 140°F)
Humidity	10% to 90% non-condensing	10% to 90% non-condensing
Optical		
Input Wavelength Range	1260 to 1620 nm	1260 to 1620 nm
Optical Input Range	-20 to 3 dBm	-20 to 3 dBm
Optical Return Loss	55 dB	55 dB
RF		
RF Output Bandwidth	5 to 300 MHz	5 to 300 MHz
RF Output Level, per Channel ¹	40 dBmV (min)	40 dBmV (min)
Flatness, Peak-to-Valley	± 0.75 dB with respect to gain slope	± 0.75 dB with respect to gain slope
Gain Slope	± 1.0 dB	± 1.0 dB
RF Gain Adjustment Range ²	0 to -31.5 in 0.5 dB steps	0 to -31.5 in 0.5 dB steps
RF Output Return Loss	16 dB (min)	16 dB (min)
RF Test Point	-20 ± 0.5 dB	-20 ± 0.5 dB
Performance		
Equivalent Input Noise	< 4.5 pA/Hz ^{0.5}	< 4.5 pA/Hz ^{0.5}
Maximum Peak NPR Variation	4 dB	4 dB
Noise-to-Power Ratio (NPR)/Dynamic Range	40/13 dB	40/13 dB
BER Dynamic Range	> 40 dB	> 40 dB
Optical Input to RF Output Terminated Isolation	≥ 60 dB	≥ 60 dB
Channel-to-Channel Isolation	5 to 300 MHz @ 60 dB	5 to 300 MHz @ 60 dB
Redundant Switching Time	50 ms	N/A
Power Requirements		
Power Consumption	7 W	7 W

NOTES:

1. RF output is based on -9 dBm optical input at 7% OMI.
2. The attenuator for each channel in the modules may be adjusted in 0.5 dB steps from 0 to 31.5 dB.

ORDERING INFORMATION

Part Number	Model Name	Description
803109	CHP-2RRXF-30-S	CHP-2RRXF-30-S: Family: CHP Max5000 [®] ; Type: Dual Channel 300 MHz Return Receivers; Front Fiber; Optical Connector: SC/APC
803110	CHP-2RRXR-30-S	CHP-2RRXR-30-S: Family: CHP Max5000; Type: Dual Channel 300 MHz Return Receivers; Rear Fiber; Optical Connector: SC/APC
803111	CHP-R2RRXF-30-S	CHP-R2RRXF-30-S: Family: CHP Max5000; Type: Redundant Dual 300 MHz Return Receivers; Front Fiber; Optical Connector: SC/APC
803112	CHP-R2RRXR-30-S	CHP-R2RRXR-30-S: Family: CHP Max5000; Type: Redundant Dual 300 MHz Return Receivers; Rear Fiber; Optical Connector: SC/APC

OPTIONS

Redundant or Non-Redundant

CORView Element Management System

RELATED PRODUCTS

CHP Chassis	Optical Patch Cords
CHP Power Supplies	Optical Passives
CHP Management Module	Installation Services

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656

COMMScope[®]

Note: Specifications are subject to change without notice.

Copyright Statement: © 2022 CommScope, Inc. All rights reserved. ARRIS, the ARRIS logo, CORView, and CHP Max5000 are trademarks of CommScope, Inc. and/or its affiliates. All other trademarks are the property of their respective owners. No part of this content may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from CommScope, Inc and/or its affiliates ("CommScope"). CommScope reserves the right to revise or change this content from time to time without obligation on the part of CommScope to provide notification of such revision or change.

1514611_CHP-R2RRX*-30-S, CHP-2RRX*-30-S_DS_RevA