



JACK, AMP-TWIST, UTP, C6A, BLACK

OBSOLETE

This product was discontinued on: June 30, 2019

Replaced By:

760241185
SL10G-BLK

NETCONNECT SL 110 Series Modular Jack, RJ45, category 6A, T568A/T568B, unshielded, no dust cover, black

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio

NETCONNECT®

Product Type

Modular jack

Product Series

SL Series

General Specifications

ANSI/TIA Category

6A

Cable Type

Unshielded

Color

Black

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Mounting

SL Series faceplates and panels

Outlet Feature

Inverted jack face

Outlet Type

Standard

Termination Tool

SL Termination tool

Termination Type

IDC

Transmission Standards

ANSI/TIA-568-C.2 | ISO/IEC 11801 Class EA

Wiring

T568A | T568B

Dimensions

Panel Cutout, recommended	14.78 x 20.32 mm (0.58 x 0.80 in)
Panel Thickness, recommended	1.6 mm 0.063 in
Height	21.5 mm 0.846 in
Width	15.25 mm 0.6 in
Depth	39.03 mm 1.537 in
Compatible Cable Diameter, maximum	9 mm 0.354 in
Compatible Insulated Conductor Diameter, maximum	1.6 mm 0.063 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	24–22 AWG
Compatible Conductor Gauge, stranded	24 AWG

Electrical Specifications

Safety Voltage Rating	150 Vac
------------------------------	---------

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	750 times
-------------------------------------	-----------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	cUL

Packaging and Weights

Included	Strain relief cap
Packaging quantity	24

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

1933476-2

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

