

BN-822810



4-1/2 IEC Coupling Element, O-Ring, screw-set

Product Classification

Product Type Coupling element

General Specifications

Inner Contact Plating Silver

Interface 4-1/2 in EIA/IEC Flange

Dimensions

Height 104.75 mm | 4.124 in

Width 104.75 mm | 4.124 in

Length 76.6 mm | 3.016 in

Electrical Specifications

Connector Impedance 50 ohm

Operating Frequency Band 1 – 5200 MHz

Environmental Specifications

Attenuation, Ambient Temperature 20 °C | 68 °F

Average Power, Ambient Temperature 20 °C | 68 °F

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Packaging and Weights

Included O-rings | Screw set

Weight, net 610 g | 1.345 lb

Regulatory Compliance/Certifications

BN-822810

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

