

## N-Type Female High Power Termination Load, 70–3000 MHz

### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type**

Termination Load

### General Specifications

**Device Type**

Termination Load

**Color**

Silver

**Interface**

N Female

### Electrical Specifications

**Return Loss, minimum**

20 dB

**Average Power, maximum**

175 W

**Impedance**

50 ohm

**Operating Frequency Band**

70 – 3000 MHz


**Peak Power, maximum**

1.5 kW

**VSWR**

1.22

### Derating Curve



## Environmental Specifications

<b>Operating Temperature</b>	-33 °C to +65 °C (-27.4 °F to +149 °F)
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP30

## Packaging and Weights

<b>Height, packed</b>	242 mm   9.528 in
<b>Width, packed</b>	165 mm   6.496 in
<b>Length, packed</b>	130 mm   5.118 in
<b>Weight, gross</b>	3.7 kg   8.157 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

