

Type N Male Positive Lock for 1/4 in LDF1-50 cable

Product Classification

Product TypeWireless and radiating connector

Product Brand HELIAX®
Product Series LDF1-50

General Specifications

Body Style Straight

Cable Family LDF1-50

Inner Contact Attachment Method Captivated

Inner Contact Plating

Interface

N Male

Mounting Angle

Outer Contact Attachment Method

Outer Contact Plating

Trimetal

Pressurizable

No

Dimensions

 Height
 20.3 mm | 0.799 in

 Width
 20.3 mm | 0.799 in


 Length
 43.1 mm | 1.697 in

 Diameter
 20.3 mm | 0.799 in

Nominal Size 1/4 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency -107 dBm @ 910 MHz

3rd Order IMD Test Method Two +43 dBm carriers

Insertion Loss Coefficient, typical 0.05

Cable Impedance50 ohmConnector Impedance50 ohm

dc Test Voltage 2200 V

Inner Contact Resistance, maximum 1 mOhm

Insulation Resistance, minimum 5000 MOhm

Operating Frequency Band 0 – 12000 MHz

Outer Contact Resistance, maximum 0.25 mOhm

Peak Power, maximum 10 kW

RF Operating Voltage, maximum (vrms) 707 V

Shielding Effectiveness -110 dB

VSWR/Return Loss



Frequency Band	VSWR	Return Loss (dB)
0-960 MHz	1.024	38.52
960-2200 MHz	1.035	35.29
2200-2700 MHz	1.035	35.29
2700-4000 MHz	1.094	26.96
4000-6000 MHz	1.21	20.5
6000-8000 MHz	1.33	17
8000-10000 MHz	1.33	17
10000-12000 MHz	1.4	15.7

Mechanical Specifications

Attachment Durability 25 cycles

Connector Retention Tensile Force 449.27 N | 101 lbf

Coupling Nut Proof Torque1.7 N-m | 15.046 in lbCoupling Nut Retention Force449.98 N | 101.16 lbf

Coupling Nut Retention Force Method MIL-C-39012C-3.25, 4.6.22

Insertion Force 27.98 N | 6.29 lbf
Insertion Force Method IEC 61169-1:15.2.4

Interface Durability 500 cycles

Interface Durability MethodIEC 61169-16:9.5Mechanical Shock Test MethodIEC 60068-2-27

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °FCorrosion Test MethodIEC 60068-2-11

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3



Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 45 g | 0.099 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Coefficient, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours

