



7-16 DIN Female Low PIM Positive Stop™ for 1-1/4 in RCT RADIAX® Radiating cable

Product Classification

|               |                                  |
|---------------|----------------------------------|
| Product Type  | Wireless and radiating connector |
| Product Brand | RADIAX®                          |

General Specifications


|                                 |                 |
|---------------------------------|-----------------|
| Body Style                      | Straight        |
| Cable Family                    | RCT6            |
| Inner Contact Attachment Method | Captivated      |
| Inner Contact Plating           | Silver          |
| Interface                       | 7-16 DIN Female |
| Mounting Angle                  | Straight        |
| Outer Contact Attachment Method | Clamp           |
| Outer Contact Plating           | Trimetal        |

Dimensions

|              |                    |
|--------------|--------------------|
| Length       | 67.31 mm   2.65 in |
| Diameter     | 51.31 mm   2.02 in |
| Nominal Size | 1-1/4 in           |

Outline Drawing

# R6PDF



## Electrical Specifications

|                                      |                      |
|--------------------------------------|----------------------|
| 3rd Order IMD at Frequency           | -107 dBm @ 910 MHz   |
| 3rd Order IMD Test Method            | Two +43 dBm carriers |
| Insertion Loss Coefficient, typical  | 0.05                 |
| Cable Impedance                      | 50 ohm               |
| Connector Impedance                  | 50 ohm               |
| dc Test Voltage                      | 4000 V               |
| Inner Contact Resistance, maximum    | 0.4 mOhm             |
| Insulation Resistance, minimum       | 10000 MOhm           |
| Operating Frequency Band             | 0 – 2700 MHz         |
| Outer Contact Resistance, maximum    | 1.5 mOhm             |
| Peak Power, maximum                  | 28.8 kW              |
| RF Operating Voltage, maximum (vrms) | 1200 V               |

## VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 50–1000 MHz    | 1.04 | 34.16            |
| 1010–2200 MHz  | 1.07 | 29.42            |
| 2200–2700 MHz  | 1.1  | 26.45            |

Mechanical Specifications

|                                   |                    |
|-----------------------------------|--------------------|
| Connector Retention Tensile Force | 800.68 N   180 lbf |
| Interface Durability              | 500 cycles         |
| Interface Durability Method       | IEC 61169-4:9.5    |
| Mechanical Shock Test Method      | IEC 60068-2-27     |

Environmental Specifications

|                                    |                                      |
|------------------------------------|--------------------------------------|
| Operating Temperature              | -55 °C to +85 °C (-67 °F to +185 °F) |
| Storage Temperature                | -55 °C to +85 °C (-67 °F to +185 °F) |
| Attenuation, Ambient Temperature   | 20 °C   68 °F                        |
| Average Power, Ambient Temperature | 40 °C   104 °F                       |
| Corrosion Test Method              | IEC 60068-2-11                       |
| Moisture Resistance Test Method    | IEC 60068-2-3                        |
| Thermal Shock Test Method          | IEC 60068-2-14                       |
| Vibration Test Method              | IEC 60068-2-6                        |

Packaging and Weights

|             |                    |
|-------------|--------------------|
| Weight, net | 421.99 g   0.93 lb |
|-------------|--------------------|

Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



\* Footnotes

|                                     |  |
|-------------------------------------|--|
| Insertion Loss Coefficient, typical | 0.05√~freq (GHz) (not applicable for elliptical waveguide) |
|-------------------------------------|--|