E95015-000 | OCAB-L1-05-B3



Fiber Optic Power Reducing Build Out Attenuator, singlemode LC/UPC, 5dB, blue

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Fiber attenuator

Product Series OCAB

General Specifications

Color Blue Interface LC/UPC

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.652.DAttenuation Tolerance± 0.5 dB

Attenuation, nominal 5 dB

Operating Wavelength

Optical Power, maximum 250 mW **Return Loss, minimum** 50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

1430 - 1625 nm

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted

Page 1 of 2



E95015-000 | OCAB-L1-05-B3

UK-ROHS

Compliant/Exempted

