



Fiber Optic Power Reducing Build Out Attenuator, singlemode SC/APC 8°, 6dB, green

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

OBSOLETE

This product was discontinued on: July 22, 2020

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber attenuator
Product Series	OCAB

General Specifications

Interface	SC/APC
------------------	--------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D
Attenuation Tolerance	± 10%
Attenuation, nominal	6 dB
Operating Wavelength	1430 – 1625 nm
Optical Power, maximum	250 mW
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

