# 204989-10



## Standard Grounding Kit for elliptical waveguide 43

## Product Classification

Product Type	Grounding kit
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

## General Specifications

Bonding Conductor Jacketing Material	PVC
Bonding Conductor Material	Copper
Cable Type	Elliptical waveguide
Color	Black
Grounding Kit Type	Standard Grounding Kits
Grounding Strap Material	Copper
Lug Attachment	Factory attached
Lug Type	One-hole lug, screw on
Thread Size	3/8 in

#### Dimensions

Bonding Conductor Length	609.6 mm   24 in
Cable Jacketing Removal Length, maximum	58.42 mm   2.3 in
Cable Jacketing Removal Length, minimum	55.88 mm   2.2 in
Compatible Diameter, maximum	50.8 mm   2 in
Compatible Diameter, minimum	49.022 mm   1.93 in
Waveguide Size	WR187   WG12   R48

# **Electrical Specifications**

Page 1 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 31, 2025

# 204989-10

Current Handling	Tested to withstand 130,000 amps peak current surge	
Current Handling Test Method	MIL-STD-1757	
Grounding, Bonding and Shielding Test Method	MIL-STD-188-124A	
Lightning Protection Test Method	IEC 1024-1	
Material Specifications		
Rivet Material	Copper	
Environmental Specifications		
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)	
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)	
Blowing Rain Test Method	MIL-STD-810, Method 506	
Corrosion Test Method	MIL-STD-1344, Method 1001	
Freezing Rain/Icing Test Method	MIL-STD-810, Method 521	
Humidity Test Method	MIL-STD-1344, Method 1002	
Immersion Test Method	IEC 60529:2001, IP68	
UV Resistance Test Method	MIL-STD-810, Method 505	
Vibration Test Method	MIL-STD-202, Method 214	
Weatherproofing Method	Butyl and electric tape	
Packaging and Weights		
Height, packed	266.7 mm   10.5 in	
Width, packed	266.7 mm   10.5 in	
Length, packed	58.42 mm   2.3 in	
Included	Grounding kit   Hardware   Lug   One roll of 2 in PVC tape   One roll of 24 in butyl rubber tape	
Packaging quantity	1	
Weight, gross	0.64 kg   1.411 lb	
Regulatory Compliance/Certifications		

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance

Page 2 of 3



# 204989-10

ROHS

UK-ROHS

Compliant Compliant



Included Products

9905-71 – Black 2 in PVC Tape, 20 ft

\* Footnotes

Grounding, Bonding and Shielding Test Method	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
Lightning Protection Test Method	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02

