# WR4550-000 | OCAB-S9-01-B3-05



Fiber Optic Power Reducing Build Out Attenuator, singlemode SC/APC 8°, 1dB, green

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

#### **OBSOLETE**

This product was discontinued on: April 11, 2018

Replaced By:

839150-000 OCAB-S2-01-B3

Fiber Optic Power Reducing Build Out Attenuator, singlemode SC/APC 8°, 1dB, green

#### **Product Classification**

Regional Availability EMEA | Latin America | North America

**Product Type** Fiber attenuator

**Product Series** OCAB

### General Specifications

Interface SC/APC

## Optical Specifications

**Fiber Mode** Singlemode

Fiber Type G.652.D Attenuation Tolerance  $\pm 0.5 dB$ 

Attenuation, nominal 1 dB

**Operating Wavelength** 1260 – 1360 nm

Optical Power, maximum250 mWReturn Loss, minimum65 dB

### **Environmental Specifications**

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

COMMSC PE°

# WR4550-000 | OCAB-S9-01-B3-05

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

