

Standard Grounding Kit for 1/2 in corrugated coaxial cable and elliptical waveguide 180 and 220

#### **Product Classification**

Product Type Grounding kit
Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

### General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Elliptical waveguide

**Color** Black

**Grounding Kit Type** Standard Grounding Kits

Grounding Strap Material Copper

Lug AttachmentField attachedLug TypeTwo-hole lug

**Thread Size** 3/8 in

#### **Dimensions**

Bonding Conductor Length1524 mm | 60 inCable Jacketing Removal Length, maximum58.42 mm | 2.3 inCable Jacketing Removal Length, minimum55.88 mm | 2.2 inCompatible Diameter, maximum16.51 mm | 0.65 inCompatible Diameter, minimum15.494 mm | 0.61 in

Nominal Size 1/2 in

**Waveguide Size** WR42 | WG20 | R220 | WR51 | WG19 | R180

ANDREW® an Amphenol company

# 241545

#### **Electrical Specifications**

**Current Handling** Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

**Lightning Protection Test Method**IEC 1024-1

Material Specifications

Rivet Material Copper

#### **Environmental Specifications**

Operating Temperature $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )Storage Temperature $-40 \,^{\circ}\text{C}$  to  $+80 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+176 \,^{\circ}\text{F}$ )

Blowing Rain Test MethodMIL-STD-810, Method 506Corrosion Test MethodMIL-STD-1344, Method 1001Freezing Rain/Icing Test MethodMIL-STD-810, Method 521Humidity Test MethodMIL-STD-1344, Method 1002

Immersion Test MethodIEC 60529:2001, IP68UV Resistance Test MethodMIL-STD-810, Method 505Vibration Test MethodMIL-STD-202, Method 214Weatherproofing MethodButyl and electric tape

Packaging and Weights

 Height, packed
 269.24 mm | 10.6 in

 Width, packed
 58.42 mm | 2.3 in

 Length, packed
 177.8 mm | 7 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

Packaging quantity 1

**Weight, gross** 0.75 kg | 1.653 lb

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



## 241545

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

#### Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

#### \* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

**Lightning Protection Test Method**Protection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02

