

42396A-2



Butterfly Hanger for 1-5/8 in coaxial cable

OBSOLETE

This product was discontinued on: December 30, 2024

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Standard butterfly hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	0
Height	70.1 mm 2.76 in
Width	38.1 mm 1.5 in
Length	88.9 mm 3.5 in
Compatible Cable Diameter Range	48.3–52 mm
Compatible Diameter, maximum	52 mm 2.047 in
Compatible Diameter, minimum	48.3 mm 1.902 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

42396A-2

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 25.4 cm | 10 in

Width, packed 39.4 cm | 15.512 in

Length, packed 17.7 cm | 6.969 in

Packaging quantity 10

Weight, gross 0.56 kg | 1.235 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power