

# DHK-158-2-P

---



Double Hanger Kit for 1-5/8 in coaxial cable, single stack; includes hardware and angle adapter

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	ValuSite™
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	1
<b>Height</b>	79 mm   3.11 in
<b>Width</b>	25.9 mm   1.02 in
<b>Length</b>	144.5 mm   5.689 in
<b>Compatible Cable Diameter Range</b>	49–51.1 mm
<b>Compatible Diameter, maximum</b>	51.1 mm   2.012 in
<b>Compatible Diameter, minimum</b>	49 mm   1.929 in
<b>Nominal Size</b>	1-5/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel 304
----------------------	------------------------------------------

## Mechanical Specifications

# DHK-158-2-P

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

### UV Resistance, minimum with no degradation

≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

### Height, packed

38.1 cm | 15 in

### Width, packed

38.1 cm | 15 in

### Length, packed

7.6 cm | 2.992 in

### Included

Angle adapter | Hardware

### Packaging quantity

1

### Weight, gross

0.57 kg | 1.257 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.andrew.com/ProductCompliance](http://www.andrew.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power