

DHK-158-4-P



Double Hanger Kit for 1-5/8 in coaxial cable, double stack; includes hardware and angle adapter

OBSOLETE

This product was discontinued on: June 30, 2013

Replaced By:

DHK-158-6-P

Double Hanger Kit for 1-5/8 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	4
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	2
Height	157.7 mm 6.209 in
Width	25.9 mm 1.02 in
Length	144.5 mm 5.689 in
Compatible Diameter, maximum	50.8 mm 2 in
Compatible Diameter, minimum	49 mm 1.929 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
------------------------------------	--------

DHK-158-4-P

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 38.1 cm | 15 in

Width, packed 38.1 cm | 15 in

Length, packed 7.6 cm | 2.992 in

Included Angle adapter | Hardware

Packaging quantity 1

Weight, gross 0.68 kg | 1.499 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power