

L4CLICK



Double Click-on Hanger for 1/2 in coaxial cable - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options available)

Product Classification

| | |
|----------------------|-----------------------------------|
| Product Type | Hanger kit |
| Product Brand | HELIAX® |
| Ordering Note | ANDREW® standard product (Global) |

General Specifications

| | |
|--------------------------|---|
| Cables per Hanger | 2 |
| Color | Black |
| Hanger Type | Click-on hanger |
| Mounting | Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod |

Dimensions

| | |
|--|--------------------|
| Maximum Stack Height | 4 |
| Height | 51.1 mm 2.012 in |
| Width | 45 mm 1.772 in |
| Length | 88.9 mm 3.5 in |
| Compatible Cable Diameter Range | 15.2–16.3 mm |
| Compatible Diameter, maximum | 16.3 mm 0.642 in |
| Compatible Diameter, minimum | 15.2 mm 0.598 in |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|------------------------------------|--------|
| Return Loss Effect, maximum | 0.1 dB |
| DTF Effect, maximum | 0.1 dB |

Material Specifications

L4CLICK

Material Type Engineered plastic

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 19 cm | 7.48 in

Width, packed 8 cm | 3.15 in

Length, packed 17 cm | 6.693 in

Packaging quantity 10

Weight, gross 0.26 kg | 0.573 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power