



SL-Series Modular Jack, RJ45, Cat6 Unshielded, Black

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio

NETCONNECT®

Product Type

Modular jack

Product Series

SL Series

General Specifications

ANSI/TIA Category

6

Cable Type

Unshielded

Color

Black

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Mounting

SL Series faceplates and panels

Mounting Note

Color matches with SL-style Black Faceplates and Surface Mount Boxes

Outlet Feature

Inverted jack face

Outlet Type

Standard

Termination Punchdowns, minimum

200 times

Termination Tool

SL Termination tool

Termination Type

IDC

Transmission Standards

ANSI/TIA-568.2-D | ISO/IEC 11801 Class E

Wiring

T568A | T568B

Dimensions

Panel Cutout, recommended

14.78 x 20.07 mm (0.58 x 0.79 in)

Panel Thickness, recommended

1.6 mm | 0.063 in

Height

16.26 mm | 0.64 in

1375055-2 | SL110-6-BK

Width	14.48 mm 0.57 in
Depth	30.48 mm 1.2 in
Compatible Insulated Conductor Diameter, maximum	1.45 mm 0.057 in
Contact Plating Thickness	1.27 μ m
Compatible Conductor Gauge, solid	24–22 AWG
Compatible Conductor Gauge, stranded	26–24 AWG

Electrical Specifications

Contact Resistance Variation, maximum	20 mOhm
Contact Resistance, maximum	100 mOhm
Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 mOhm
Remote Powering	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles
Safety Voltage Rating	150 Vac

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Polycarbonate
Termination Contact Plating	Tin

Mechanical Specifications

Plug Retention Force, minimum	50 N 11.24 lbf
Plug to Jack Mating Cycles	Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

1375055-2 | SL110-6-BK

Flammability Rating

UL 94 V-0

Safety Standard

UL | cUL

Packaging and Weights

Included

Strain relief cap

Packaging quantity

1

Packaging Type

Bag

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

RCM

Compliant to electrical safety & telecommunications requirements

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

