



JACK, AMP-TWIST, UTP, C6A, RED

## OBSOLETE

This product was discontinued on: June 30, 2019

### Replaced By:

760241189  
SL10G-RED

NETCONNECT SL 110 Series Modular Jack, RJ45, category 6A, T568A/T568B, unshielded, no dust cover, red

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

### Portfolio

NETCONNECT®

### Product Type

Modular jack

### Product Series

SL Series

## General Specifications

### ANSI/TIA Category

6A

### Cable Type

Unshielded

### Color

Red

### Conductor Type

Solid | Stranded

### Integrated Dust Cover Type

None

### Mounting

SL Series faceplates and panels

### Outlet Feature

Inverted jack face

### Outlet Type

Standard

### Termination Tool

SL Termination tool

### Termination Type

IDC

### Transmission Standards

ANSI/TIA-568-C.2 | ISO/IEC 11801 Class EA

### Wiring

T568A | T568B

## Dimensions

<b>Panel Cutout, recommended</b>	14.78 x 20.32 mm (0.58 x 0.80 in)
<b>Panel Thickness, recommended</b>	1.6 mm   0.063 in
<b>Height</b>	21.5 mm   0.846 in
<b>Width</b>	15.25 mm   0.6 in
<b>Depth</b>	39.03 mm   1.537 in
<b>Compatible Cable Diameter, maximum</b>	9 mm   0.354 in
<b>Compatible Insulated Conductor Diameter, maximum</b>	1.6 mm   0.063 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	24–22 AWG
<b>Compatible Conductor Gauge, stranded</b>	24 AWG

## Electrical Specifications

<b>Safety Voltage Rating</b>	150 Vac
------------------------------	---------

## Material Specifications

<b>Contact Base Material</b>	Beryllium copper
<b>Contact Plating Material</b>	Gold
<b>Material Type</b>	Polycarbonate

## Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	750 times
-------------------------------------	-----------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	cUL

## Packaging and Weights

<b>Included</b>	Strain relief cap
<b>Packaging quantity</b>	24

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# 1933476-7

---

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

