



## SL-Series Modular Jack, RJ45, Cat6 Shielded, Gray

### Product Classification

**Regional Availability**

Asia | Australia/New Zealand | EMEA | Latin America

**Portfolio**

NETCONNECT®

**Product Type**

Modular jack

**Product Series**

SLX Series

### General Specifications

**ANSI/TIA Category**

6

**Cable Type**

Shielded

**Color**

Gray

**Conductor Type**

Solid | Stranded

**Integrated Dust Cover Type**

None

**Mounting**

SL Series faceplates and panels

**Mounting Note**

Color matches with SL-style Gray Faceplates and Surface Mount Boxes

**Outlet Type**

Standard

**Termination Punchdowns, minimum**

5 times

**Termination Tool**

SL Termination tool

**Termination Type**

IDC

**Transmission Standards**

ANSI/TIA-568-C.2 | ISO/IEC 11801 Class E

**Wiring**

T568A | T568B

### Dimensions

**Panel Cutout, recommended**

14.78 x 20.07 mm (0.58 x 0.79 in)

**Panel Thickness, recommended**

1.6 mm | 0.063 in

**Height**

16.13 mm | 0.635 in

**Width**

14.44 mm | 0.569 in

# 2153448-4 | SLX-6S-GY

<b>Depth</b>	36.8 mm   1.449 in
<b>Compatible Cable Diameter, maximum</b>	8.5 mm   0.335 in
<b>Compatible Insulated Conductor Diameter, maximum</b>	1.6 mm   0.063 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	26–22 AWG
<b>Compatible Conductor Gauge, stranded</b>	26–24 AWG

## Electrical Specifications

<b>Remote Powering</b>	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
<b>PoE Durability</b>	Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles

## Material Specifications

<b>Contact Base Material</b>	Beryllium copper
<b>Contact Plating Material</b>	Gold
<b>Material Type</b>	Polycarbonate   Zamak

## Mechanical Specifications

<b>Plug to Jack Mating Cycles</b>	Complies to IEC 60603-7 series
-----------------------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Flammability Rating</b>	UL 94 V-0

## Packaging and Weights

<b>Packaging Material</b>	Standard
<b>Packaging quantity</b>	24
<b>Packaging Type</b>	Bag   Box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

ROHS  
UK-ROHS

Compliant  
Compliant

