

# SHK-78-2-P



Single Hanger Kit for 7/8 in coaxial cable, double stack; includes hardware and angle adapter

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	ValuSite™
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Harmonized System (HS) Code</b>	85366910 (Coaxial cable and other coaxial electric conductors)
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	2
<b>Height</b>	101.6 mm   4 in
<b>Width</b>	26.2 mm   1.031 in
<b>Length</b>	60.2 mm   2.37 in
<b>Compatible Cable Diameter Range</b>	26.7–28.2 mm
<b>Compatible Diameter, maximum</b>	28.2 mm   1.11 in
<b>Compatible Diameter, minimum</b>	26.7 mm   1.051 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel 304
----------------------	--

# SHK-78-2-P

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 15 cm | 5.906 in

**Width, packed** 15 cm | 5.906 in

**Length, packed** 3 cm | 1.181 in

**Included** Angle adapter | Hardware

**Packaging quantity** 1

**Weight, gross** 0.45 kg | 0.992 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power