

# H5PNM

---



Type N Male with gas barrier for 7/8 in HJ5-50 air dielectric cable

## OBSOLETE

This product was discontinued on: April 1, 2014

### Replaced By:

H5PNM-S

Type N Male with gas barrier for 7/8 in HJ5-50 air dielectric cable

## Product Classification

<b>Product Type</b>	Air coaxial connector
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Body Style</b>	Straight
<b>Cable Family</b>	HJ5-50
<b>Gas Barrier</b>	Yes
<b>Inner Contact Attachment Method</b>	Self-tapping
<b>Inner Contact Plating</b>	Gold
<b>Interface</b>	N Male
<b>Mounting Angle</b>	Straight
<b>Outer Contact Attachment Method</b>	Tab-flare
<b>Outer Contact Plating</b>	Silver

## Dimensions

<b>Length</b>	83.312 mm   3.28 in
<b>Diameter</b>	34.798 mm   1.37 in
<b>Nominal Size</b>	7/8 in

# H5PNM

---

## Electrical Specifications

<b>Insertion Loss, typical</b>	0.05 dB
<b>Average Power at Frequency</b>	0.6 kW @ 900 MHz
<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>dc Test Voltage</b>	2 kV
<b>Insulation Resistance, minimum</b>	5000 MOhm
<b>Operating Frequency Band</b>	0 – 5200 MHz
<b>Peak Power, maximum</b>	10 kW
<b>RF Operating Voltage, maximum (vrms)</b>	707 V

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>0–1000 MHz</b>	1.03	40
<b>1000–2200 MHz</b>	1.03	38
<b>2200–4000 MHz</b>	1.12	25
<b>4000–7000 MHz</b>	1.23	20
<b>7000–10000 MHz</b>	1.44	15

## Mechanical Specifications

<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	MIL-C-39012, Section 4.6.12
<b>Mechanical Shock Test Method</b>	MIL-STD-202, Method 213, Test Condition I

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +150 °C (-40 °F to +302 °F)
<b>Storage Temperature</b>	-70 °C to +100 °C (-94 °F to +212 °F)
<b>Corrosion Test Method</b>	MIL-STD-202, Method 101, Test Condition B
<b>Moisture Resistance Test Method</b>	MIL-STD-202, Method 106
<b>Thermal Shock Test Method</b>	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
<b>Vibration Test Method</b>	MIL-STD-202, Method 204, Test Condition B

## Packaging and Weights

# H5PNM

---

**Weight, net**

0.33 kg | 0.728 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015



**Classification**

Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Insertion Loss, typical** 0.05v̄freq (GHz) (not applicable for elliptical waveguide)