

# H9MB-602

---

6-1/8 in EIA Male Flange with gas barrier for 5 in HJ9-50 air dielectric cable

## OBSOLETE

This product was discontinued on: April 1, 2014

## Product Classification

<b>Product Type</b>	Air coaxial connector
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Body Style</b>	Straight
<b>Cable Family</b>	HJ9-50
<b>Gas Barrier</b>	Yes
<b>Inner Contact Attachment Method</b>	Thread-in stub
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	6-1/8 in EIA Male Flange
<b>Mounting Angle</b>	Straight
<b>Outer Contact Attachment Method</b>	Tab-flare
<b>Outer Contact Plating</b>	Unplated

## Dimensions

<b>Length</b>	241.3 mm   9.5 in
<b>Diameter</b>	206.248 mm   8.12 in
<b>Nominal Size</b>	5 in

## Electrical Specifications

<b>Insertion Loss, typical</b>	0.05 dB
<b>Average Power at Frequency</b>	57.0 kW @ 900 MHz
<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>dc Test Voltage</b>	28 kV
<b>Insulation Resistance, minimum</b>	5000 MOhm

# H9MB-602

---

<b>Operating Frequency Band</b>	0 – 860 MHz
<b>Peak Power, maximum</b>	1890 kW
<b>RF Operating Voltage, maximum (vrms)</b>	9721 V

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>45–500 MHz</b>	1.03	39.3
<b>510–1000 MHz</b>	1.03	39.3
<b>1010–1500 MHz</b>	1.03	39
<b>1510–2200 MHz</b>	1.03	38.6
<b>2210–2500 MHz</b>	1.04	35

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +150 °C (-40 °F to +302 °F)
<b>Storage Temperature</b>	-70 °C to +100 °C (-94 °F to +212 °F)

## Packaging and Weights

<b>Weight, net</b>	16.78 kg   36.994 lb
--------------------	----------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

<b>Insertion Loss, typical</b>	0.05v̄freq (GHz) (not applicable for elliptical waveguide)
--------------------------------	--