

Type N Female Bulkhead for 1/4 in LDF1-50 cable

Product Classification

Product TypeWireless and radiating connector

Product Brand HELIAX®
Product Series LDF1-50

General Specifications

Body StyleStraightCable FamilyLDF1-50Inner Contact Attachment MethodSolderInner Contact PlatingGold

InterfaceN FemaleMounting AngleStraightOuter Contact Attachment MethodSelf-flareOuter Contact PlatingSilverPressurizableNo

Dimensions


 Length
 52.07 mm | 2.05 in

 Diameter
 15.75 mm | 0.62 in

Nominal Size 1/4 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency-112 dBm @ 910 MHz3rd Order IMD Test MethodTwo +43 dBm carriersAverage Power at Frequency0.6 kW @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage2200 VInner Contact Resistance, maximum1 mOhmInsulation Resistance, minimum5000 MOhmOperating Frequency Band0 - 6000 MHzOuter Contact Resistance, maximum0.25 mOhm

Peak Power, maximum10 kWRF Operating Voltage, maximum (vrms)707 VShielding Effectiveness-110 dB

Mechanical Specifications

Connector Retention Tensile Force449.27 N | 101 lbfCoupling Nut Proof Torque1.7 N-m | 15.046 in lbCoupling Nut Proof Torque MethodIEC 61169-16:9.3.11



Coupling Nut Retention Force445 N | 100.04 lbfCoupling Nut Retention Force MethodIEC 61169-16:9.3.11Insertion Force124.55 N | 28 lbfInsertion Force MethodIEC 61169-16:9.3.5

Interface Durability500 cyclesInterface Durability MethodIEC 61169-4:17

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °FCorrosion Test MethodIEC 60068-2-11

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 89 g | 0.196 lb

Regulatory Compliance/Certifications

CHINA-ROHS Below maximum concentration value

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Agency



* Footnotes

Immersion Depth Immersion at specified depth for 24 hours

