C-20-UW-N-AI6



Product Classification

20 dB, Air Directional Coupler, 555–6000 MHz

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Directional coupler
General Specifications	
Device Type	Coupler
Application	Indoor/Outdoor
Color	White
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal
Dimensions	
Height	22 mm 0.866 in
Width	72 mm 2.835 in
Length	159 mm 6.26 in
Electrical Specifications	
3rd Order IMD	-163 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss at Frequency Band	0.3 dB @ 555-6000 MHz
Average Power, maximum	200 W
Coupling	20 dB
Coupling Tolerance	±1.35dB
Impedance	50 ohm
Isolation at Frequency Band	30 dB @ 4900-6000 MHz 35 dB @ 555-2700 MHz 36 dB @ 3800-4900 MHz 38 dB @ 2700-3800 MHz
Operating Frequency Band	555 – 6000 MHz

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023



C-20-UW-N-AI6

Peak Power, maximum	1 kW
Reflected Power, maximum	200 W
VSWR at Frequency Band	1.25:1 @ 2700-3800 MHz 1.2:1 @ 555-2700 MHz 1.3:1 @ 3800-6000 MHz
Mechanical Specifications	

Coupling Nut Proof Torque	4.5 N-m 39.828 in lb
---------------------------	------------------------

Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67

Packaging and Weights

Height, packed	45 mm 1.772 in
Width, packed	98 mm 3.858 in
Length, packed	180 mm 7.087 in
Weight, gross	0.44 kg 0.97 lb
Weight, net	0.38 kg 0.838 lb

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015



Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023

