

C-8-CPUSE-N-AI6

8 dB, Air Directional Coupler, 555–2700 MHz



OBSOLETE

This product was discontinued on: October 31, 2019

Replaced By:

C-8-UW-N-AI6

8 dB, Air Directional Coupler, 555–6000 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Directional coupler

General Specifications

Device Type

Coupler

Application

Indoor/Outdoor

Color

Silver

Inner Contact Plating

Silver

Interface

N Female

Outer Contact Plating

Trimetal

Dimensions

Height

22 mm | 0.866 in

Width

75 mm | 2.953 in

Length

155 mm | 6.102 in

Electrical Specifications

3rd Order IMD

-160 dBc

3rd Order IMD Test Method

Two +43 dBm carriers

C-8-CPUSE-N-A16

Insertion Loss at Frequency Band	1.1 dB @ 555–2700 MHz
Return Loss, minimum	20.8 dB
Average Power, maximum	200 W
Coupling	8 dB
Coupling Tolerance	±1.0dB @ 698–2700 MHz ±2.0dB @ 555–698 MHz
Impedance	50 ohm
Isolation at Frequency Band	28 dB @ 555–2700 MHz
Operating Frequency Band	555 – 2700 MHz
Peak Power, maximum	1 kW
Reflected Power, maximum	70 W
VSWR	1.2

Mechanical Specifications

Coupling Nut Proof Torque	4.5 N-m 39.828 in lb
----------------------------------	------------------------

Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	40 mm 1.575 in
Width, packed	90 mm 3.543 in
Length, packed	180 mm 7.087 in
Volume	648 cc 39.543 in ³
Weight, gross	0.42 kg 0.926 lb
Weight, net	0.38 kg 0.838 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

C-8-CPUSE-N-A16

