

209800-17B



Self-locking Hanger for 1/2 in RXL4 RADIAX® Radiating cable

OBSOLETE

This product was discontinued on: March 31, 2025

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 1
Color Black
Hanger Type Self locking hanger

Dimensions

Maximum Stack Height 2
Height 35.3 mm | 1.39 in
Width 19.6 mm | 0.772 in
Length 22.6 mm | 0.89 in
Compatible Diameter, maximum 19.5 mm | 0.768 in
Compatible Diameter, minimum 16.8 mm | 0.661 in
Nominal Size 1/2 in

Material Specifications

Material Type Polyamide PA12

Mechanical Specifications

Maximum Load 650 N | 146.126 lbf

Environmental Specifications

209800-17B

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Flammability Test Method	UL 94-HB
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	≥500 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	16.5 cm 6.496 in
Width, packed	11 cm 4.331 in
Length, packed	19 cm 7.48 in
Packaging quantity	100
Weight, gross	0.7 kg 1.543 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power