

FT-16SM-001

HELIAX® FiberFeed® Bend Insensitive Singlemode Fiber DLC to DLC 16-Fiber Cable Assembly with pulling grip



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Series	RFFT
Ordering Note	CommScope® non-standard product

General Specifications


Construction Type	Discrete fiber trunk
Interface, Connector A	DLC
Interface Feature, connector A	Uniboot
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Uniboot
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	16

Dimensions

Cable Assembly Length Range (m)	5 – 170
Diameter Over Jacket	10.28 mm 0.405 in

Ordering Tree

FT-16SM-001



Mechanical Specifications

Minimum Bend Radius 103 mm | 4.055 in

Minimum Bend Radius, furcation 30 mm | 1.181 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Indoor | Outdoor

Packaging and Weights

Cable weight 91 kg/km | 61.149 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)