


BHS-158



Single Block Hanger for 1-5/8 in coaxial cable

OBSOLETE

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	Single block hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	51.1 mm 2.012 in
Width	71.1 mm 2.799 in
Length	81 mm 3.189 in
Compatible Cable Diameter Range	49–51.1 mm
Compatible Diameter, maximum	51.1 mm 2.012 in
Compatible Diameter, minimum	49 mm 1.929 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

BHS-158

Material Specifications

Material Type Engineered plastic

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 5.1 cm | 2.008 in

Width, packed 25.4 cm | 10 in

Length, packed 25.4 cm | 10 in

Packaging quantity 10

Weight, gross 1.02 kg | 2.249 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power