

MC-SA18-B



Stand-off Arm with U-bolts, 18 in

Product Classification

Product Type Support arms for ring mount

General Specifications

Mounting Ring mount

Pipe, quantity 0

Dimensions


Height 254 mm | 10 in

Width 254 mm | 10 in

Length 457.2 mm | 18 in

Stand-off Distance 457.2 mm | 18 in

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

MC-SA18-B

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Criteria	One 72 in x 8 in panel antenna per sector
Wind Rating Test Method	TIA/EIA-222-G

Packaging and Weights

Included	Hardware Stand-off arms U-bolts
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	------------------------------------------------