## 760242322 | OTE210-08MH-18-S12-G-W



# Mini-OTE 210-Series, Optical Terminal Enclosure, 8-port full-size connector, 1x8 splitter, 12 smouv splice trays, grey, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

**Product Type** Access terminal, without splitter/tap

**Product Series** Mini-OTE 200

General Specifications

Cable Type No cable (stubless)

Cable, quantity 0

**Distribution Type** 1 x 8 splitter

Enclosure Color Gray

 Mounting
 Handhole
 | Pole
 | Wall

 Port Type
 Hardened full-size SC/APC

Port, quantity 6

Splice Tray Included, quantity

Splicing Type, SupportedSingle fusionSplit RatioSymmetrical

Splitter, quantity 1

Stub Type No tail

**Dimensions** 

 Height
 358.5 mm | 14.114 in

 Width
 166 mm | 6.535 in

 Depth
 129.3 mm | 5.091 in


COMMSCOPE®


## 760242322 | OTE210-08MH-18-S12-G-W

Cable Length, stub


0 ft (0 m)

## Dimension Drawing





## Ordering Tree



Material Specifications

**Enclosure Material Type**Glass filled polypropylene (GF-PP)

Optical Specifications

**Fiber Type** G.652.D

Page 2 of 4

## 760242322 | OTE210-08MH-18-S12-G-W

**Operating Wavelength Range** 1260 – 1635 nm

Attenuation Terminal Connectors, maximum0.4 dBInsertion Loss, Terminal Connector, typical0.16 dBReturn Loss, Connector, minimum65 dB

### **Environmental Specifications**

**Operating Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +65 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +149 \, ^{\circ}\text{F})$ 

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground | Buried

**Qualification Standards** IEC 60529, IP68 + 3 m waterhead

UV Resistance UV stabilized

Packaging and Weights

Included Cable termination unit (2) | Enclosure (1) | Fiber pigtail cassette

(1) | Splice Cassette (2)

Packaging quantity

Packaging Type Box | Carton

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

CW8094-002 – TENIO™ Cable Termination Unit kit TENIO-CTU-L-(10)



**COMMSCOPE®** 

Page 3 of 4

## CW8094-002 | TENIO-CTU-L-(10)





### **Product Classification**

Regional Availability EMEA

**Product Type** Cable termination kit

Product Series TENIO

### **Environmental Specifications**

Environmental Space Outdoor

### Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



