

# SHK-24-1-P-10



Hanger Kit for single stack of RFF cable; includes ten sets of hardware, angle adapters and rubber grommets

**OBSOLETE**

## Product Classification

|                      |            |
|----------------------|------------|
| <b>Product Type</b>  | Hanger kit |
| <b>Product Brand</b> | HELIAX®    |

## General Specifications

|                          |                 |
|--------------------------|-----------------|
| <b>Cables per Hanger</b> | 1               |
| <b>Color</b>             | Black           |
| <b>Hanger Type</b>       | Composite clamp |
| <b>Mounting</b>          | M8 hardware     |

## Dimensions

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Maximum Stack Height</b>         | 1                  |
| <b>Height</b>                       | 55.1 mm   2.169 in |
| <b>Width</b>                        | 59.9 mm   2.358 in |
| <b>Length</b>                       | 171 mm   6.732 in  |
| <b>Compatible Diameter, maximum</b> | 23.6 mm   0.929 in |
| <b>Compatible Diameter, minimum</b> | 24.1 mm   0.949 in |

## Electrical Specifications

|                                    |        |
|------------------------------------|--------|
| <b>Return Loss Effect, maximum</b> | 0.1 dB |
| <b>DTF Effect, maximum</b>         | 0.1 dB |

## Material Specifications

|                      |  |
|----------------------|--|
| <b>Material Type</b> | EPDM rubber   Engineered plastic   Stainless steel |
|----------------------|--|

## Mechanical Specifications

# SHK-24-1-P-10

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

### UV Resistance, minimum with no degradation

≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

### Height, packed

0 cm | 0 in

### Width, packed

0 cm | 0 in

### Length, packed

0 cm | 0 in

### Included

Angle adapter | Hardware | Rubber grommet

### Packaging quantity

10

### Weight, gross

2.8 kg | 6.173 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power