

NOVUX™ Hardened Indexing Terminal, Full-size Adapter ports, 12F, 1:4 Splitter, 1 Forward port, 1 Reverse port, Dielectric flat loose tube, 1250 ft /381 m HMFOC plug (female/no pin) tail

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ HXT fiber indexing terminals are available with 1:4 or 1:8 splitter and optional multi-use ports, Index Only and Index Branching 2 to 6 fiber solutions
- Available with flat dielectric and flat toneable/locatable dielectric cable
- NOVUX™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

Product Classification

Regional Availability

Asia | EMEA | Latin America | North America

Product Type Access terminal, with splitter/tap

 Product Brand
 NOVUX™

 Product Series
 HXT

 Minimum Order Quantity
 1

General Specifications

Cable Type Dielectric - Flat - Loose Tube

Cable, quantity 1

Distribution Type 1 x 4 splitter

Drop Port TypeHardened full-size SC/APC

Drop Port, quantity 4

Enclosure Color Black (RAL 9005)

Forward Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Forward Port, quantity

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

Port, quantity 5

COMMSCOPE®

Reverse Port Type Hardened full-size SC/APC

Reverse Port, quantity 1

Splitter, quantity 1

Stub Type Hardened multi-fiber (HMFOC) plug, female/no pin

Dimensions

 Height
 80 mm | 3.15 in


 Width
 157 mm | 6.19 in


 Length
 192 mm | 7.58 in

 Cable Length, stub
 1250 ft (381 m)

Cable Outer Diameter 4.3 x 8.0 mm (0.17 x 0.31 in)

Dimension Drawing






Port Configuration

NOVUX HT	TECHNOLOGIES AVAILABLE	SMALL	MEDIUM	LARGE
	Fiber indexing	12 fiber index only, 1f	12 fiber 1:4	12 fiber 1:8
		12 fiber index only, 2f	12f multi-use 2f + 1:4	12 fiber multi-use, 3f +1:4
		12 fiber index only, 3f	24f multi-use 2f	12 fiber multi-use, 4f +1:4
HXT Series		12 fiber index only, 4f	24f multi-use 3f	12 fiber multi-use, 2f +1:8
		12 fiber multi-use, 2f	24f multi-use 4f	
		12 fiber branching, 2 to 6f per port		

Ordering Tree



Material Specifications

Enclosure Material Type Hardened plastic

Optical Specifications

Fiber Type G.657.A1/A2

Operating Wavelength Range 1260 – 1635 nm

Attenuation Single Ports, maximum 0.4 dB

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

COMMSCOPE®

Attenuation Splitter, maximum7.1 dBAttenuation Terminal Connectors, maximum0.4 dBInsertion Loss, Stub Connector, maximum0.65 dBReturn Loss, Single Ports, minimum55 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$

Relative Humidity 5%–100%, condensing

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type

Box | Universal spool, cardboard: terminal is on top of the spool, stub deploys

first

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

