MLOC-4-F1BNHM-2M



HELIAX® M-LOC Multiport cluster 4 ports SureFlex® cable assembly with Integrated Birdproofing Shell with interface type M-LOC latching male to 4.3-10 male, size 1/4", length 2 meters

Product Classification

Product Type HELIAX® MLOC cluster, SureFlex® Premium, static PIM

Product Brand HELIAX® | SureFlex®

Product Series MLOC

General Specifications

Attachment, Connector A Factory attached

Attachment, Connector B Factory attached

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector AM-LOC MaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 2 m | 6.562 ft

Nominal Size 1/4 in

Electrical Specifications

3rd Order IMD Static -119 dBm

3rd Order IMD Static Test MethodTwo +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000-3000 MHz	1.135	23.98	1.07	30	1.09
3000-4200 MHz	1.222	20.01	1.11	26	0.98

Page 1 of 2



MLOC-4-F1BNHM-2M

4200-5000 MHz 1.25 19.08 1.12 25 0.82

Mechanical Specifications

Minimum Bend Radius, multiple Bends25.4 mm | 1 inMinimum Bend Radius, single Bend25.4 mm | 1 in

Environmental Specifications

Installation temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-67 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-67 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



Included Products

FSJ1-50A - FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in,

black PE jacket

