

SSC-760252485 | High Capacity Radio Enclosure - HCRE, Configurable



Middle of Pole Concealment Enclosure that is configurable for small cell equipment. Ideal for Multi Tenant

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

Customer configurable enclosure to support radio equipment.

Up to 2 Optional Fan Kits available.

Please reach out to your ANDREW representative for custom configurations and additional equipment compatibility.

Includes mounting hardware to be attached to wood poles via through bolt or metal poles up 10.75" OD.

Product Classification

Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Access	Double door
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metal
Compatible Smart Devices	Environmental Monitoring WIFI
Cooling	Passive Cooling
Doors, quantity	2
Front Door Type	Single hinged
Growth Configuration	Unloaded
Mounting	Back to Back Direct attach Pole Rack Wall
Mounting Options	Concrete poles Fluted poles Metal poles Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	6302 ABB CC1600 APAF CCI PSU-1200W-48-N DELTA 1.0 DELTA 2.0 DELTA 3.0 FPAE
Radio Compatibility, Ericsson	220x 440x 4415 4426 4435 4449 4455 4478 8843 8863 Diplexer Power Di
Radio Compatibility, Nokia	AAHA AHBCA AHGCC AHCA AHFB AHFIA AHFIB AHFIC AHIA AHIB AHLBA

SSC-760252485 | High Capacity Radio Enclosure - HCRE, Configurable

micro

Radio Compatibility Samsung RF4402D-D1A | RF4437D | RF4439D | RF4440D | RF4442D | RFV01U-D1A | RFV01U-D2A | RT2201

Radios Included None

Dimensions

Height 1,778 mm | 70 in

Width 609.6 mm | 24 in

Depth 609.6 mm | 24 in

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.661 m³ | 23.34 ft³